


# AVERY DENNISON MARKETING SPECIFICATION

TOLERANCES IN. = .030 IN.  
MM = 0.7 mm



NOT TO SCALE

|                            |   |
|----------------------------|---|
| TENSILE STRENGTH: (LOOPED) | 50 LBSF. / 22.7 KGF. MINIMUM PER MIL-S-23190.                         |
| OPERATING TEMP. RANGE:     | -40 °F (-40 °C) TO 220 °F (105 °C)                                    |
| MATERIAL:                  | IMPACT MODIFIED NYLON 6/6<br>PER ASTM D4066 - HEAT STABILIZED, BLACK  |
| WEIGHT:                    | 1.7 GRAMS/EACH  |
| BUNDLE DIAMETER:           | 1/16" - 1-3/4"  |
| MOUNTING:                  | N/A   |
| APPLICATION TOOL:          | 12001 - HAND INSTALLATION TOOL<br>12500 - PNEUMATIC INSTALLATION TOOL |
| TOOL TENSION SETTING:      | 6-8   |
| PACKAGED IN:               | 1000/BAG, 5 BAGS/MASTER   |



FASTENER DIVISION  
FITCHBURG, MA 01420 U.S.A.  
TEL. 1-800-225-5913  
MA. 978-353-8157

DESCRIPTION:

CONVOLUTED TUBING TIE, BLACK

APPROVALS:

T.S.: *[Signature]*

ENG'RG: *[Signature]*

8.14.07

STOCK NO.

20093

REV.

A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20093-0](#)