





AVERY DENNISON MARKETING SPECIFICATION

HISTORY


REV.	DATE	DESCRIPTION
A	1-5-18	RELEASE TO PRODUCTION



ASSEMBLED VIEW



MOUNTING HOLE DETAIL



11	△	FLAMMABILITY:	HB-2 PER FMVSS302
12	△	TENSILE STRENGTH:	50 LBF / 22.7 KGF MIN.
		MOUNTING:	SEE MOUNTING HOLE DETAIL AND ASSEMBLED VIEW
		OPERATING TEMP RANGE:	-40°F (-40°C) TO 302°F (150°C)
		WEIGHT:	3.2 GRAMS
		BUNDLE DIAMETER:	Ø 1.6mm TO Ø 44.5mm
		TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
		TOOL TENSION SETTING:	6 - 8
		PACKAGING:	500/BAG, 10 BAGS/MASTER

NOTES:

1) △ INDICATES SPECIAL CHARACTERISTICS

APPROVALS:	ENG. APPR. <i>[Signature]</i> 1/5/18
	Q.A. APPR. <i>Curtis Vaillancourt</i> 1/5/18

SPECIFIED TOLERANCES ARE:

.XX ± .03 INCHES	.X ± 0.7 mm
.XXX ± .010 INCHES	.XX ± 0.25 mm
ANGULAR: ± 2°	

MATERIAL **NYLON 6/6, IMPACT MODIFIED, HEAT STABILIZED**

COLOR **BROWN**



AVERY DENNISON

FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL. 1-800-225-5913
FAX. 978-353-8157

DESCRIPTION **FIR TREE STANDOFF TIE, HIGH HEAT**

STOCK NO. **20106-HHBN**

REV. **A**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20106-0](#)