



# **AVERY DENNISON MARKETING SPECIFICATION**



THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

## **HISTORY**

REV.	DATE	DESCRIPTION
A	2/23/07	RELEASE TO PRODUCTION
B	8/24/07	INCREASE CAPACITY
C	01/16/08	REVISED MODEL, PART WEIGHT 1.9 GRAMS WAS 1.8 GRAMS



### **DETAIL A: MOUNTING SLOT**



MOUNTING:	SEE DETAIL A
TENSILE STRENGTH:	50 LBF / 22.7 KGF MIN.
OPERATING TEMP RANGE:	-40°F (-40°C) TO 220°F (105°C)
WEIGHT:	1.9 GRAMS
BUNDLE DIAMETER:	Ø 1.6MM TO Ø 44.5MM
INSTALLATION TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL
TOOL TENSION SETTING:	6 - 8
PACKAGING:	500/BAG, 10 BAGS/MASTER

APPROVALS:	ENG. APPR. <i>Paul Hertzberg</i> 1/16/08
	Q.A. APPR. <i>[Signature]</i> 1-16-08

GENERAL TOLERANCE  
UNLESS SPECIFIED ± .02 [0.5mm]

.X ± — .XXX ± —  
 .XX ± — ANGULAR: ± 3°

MATERIAL  
**IMPACT MODIFIED NYLON 6/6**

COLOR  
**BLACK**



FASTENER DIVISION  
 FITCHBURG, MA 01420 U.S.A.  
 TEL: 1-800-225-5913  
 FAX: 978-353-8157

DESCRIPTION  
**ADGT CONNECTOR TIE**

STOCK NO. **20113** REV. **C**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20113-0](#)