



# **AVERY DENNISON MARKETING SPECIFICATION**

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.

## **HISTORY**

REV.	DATE	DESCRIPTION
A	10-11-12	RELEASED



MOUNTING:	Ø 6.60MM ± 0.25MM HOLE AND 6.35MM HEX HOLE. PANEL THICKNESS OF 0.7MM TO 7.0MM.			
TENSILE STRENGTH:	50 LBF / 222.4N MIN.			
TEMPERATURE RANGE:	-40°F (-40°C) TO 239°F (115°C) CONTINUOUS AND 257°F (125°C) AT MAXIMUM EXPOSURE			
WEIGHT:	2.62 GRAMS EACH			
BUNDLE DIAMETER:	Ø 1/16"(1.6MM) TO Ø 1- 7/8" (47.6MM)			
INSTALLATION TOOL:	12001 - HAND TOOL 12500 - PNEUMATIC TOOL			
TOOL TENSION SETTING:	6 - 8			
PACKAGING:	500/BAG, 10 BAGS/MASTER			
APPROVALS:		ENG. APPR. <i>[Signature]</i> 10/11/12 Q.A. APPR. <i>[Signature]</i> 10/15/12	 <b>AVERY DENNISON</b> <small>FASTENER DIVISION FITCHBURG, MA 01420 U.S.A. TEL. 1-800-225-5913 FAX. 978-353-8157</small>	
SPECIFIED TOLERANCES		MATERIAL		DESCRIPTION <b>25MM LIFT OFFSET TIE - STD</b>
INCHES		NYLON 6/6, IMPACT MODIFIED, HEAT STABILIZED		
MM		COLOR		
.XX ± .03 .X ± .7 .XXX ± .01 .XX ± .25 ANGULAR: ± 2°		BLACK		
		STOCK NO.	REV.	
		20132-0	A	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20132-0](#)