






- NOTES:
- PIN HOUSING WITH KEYWAY CAN BE ROTATED 45° 8 POSITIONS.
 - Ø 0.04 [1.0mm] X 0.08 [2.0mm] DEEP HOLE IN PIN FOR SOLDERING.
 - Ø 0.21 [5.4mm] ID X 0.39 [10.0mm] LONG CABLE CLAMP TUBE NOT SHOWN.
 - MATERIALS:
TWO PIECE HANDLE & PIN HOUSING - ZINC ALLOY, NICKEL PLATED
INSERT - THERMOPLASTIC, BLACK
PINS - COPPER ALLOY, TIN PLATED
FLEX RELIEF - THERMOPLASTIC, BLACK
CABLE CLAMP TUBE - COPPER ALLOY
SCREW - STEEL, NICKEL PLATED
 - SHIPPED ASSEMBLED.
 - THESE PRODUCTS ARE RoHS COMPLIANT.



CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH SPEC No.			MATERIAL SPEC No.	
					FIRST USED ON		SCALE 3:2		Switchcraft®
					DATE DRAWN 5-Jun-13	BY TO	CHKD TO 6-5-13	APVD TJK 6-6-13	
					NAME MALE DIN 5-7 PIN CORD PLUG CONNECTOR, RoHS			PART No. 05DL_MX, 12DL_MX, 15DL_MX SERIES	REV B
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING				
REVISIONS									
B	28010	3/14/18	TJK	TJK					
A	26000	3/3/06	TJK	TJK					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[05DL5MX](#)