



SECTION A-A

MATERIALS:

BODY, SLEEVE AND SHIELDED HANDLE - COPPER ALLOY, NICKEL PLATED
 SPRINGS - SPECIAL COPPER ALLOY
 BUSHING AND FLANGE - PLATED COPPER ALLOY
 INSULATION - THERMOPLASTIC
 CLAMP TERMINALS - TIN-PLATED COPPER ALLOY

NOTE:

SAME AS 80, EXCEPT SHIELDED HANDLE AND INSULATOR.

CUSTOMER DRAWING



STAR SYMBOL DENOTES CRITICAL DIMENSION

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES
 - TWO PLACE DECIMALS ± 0.01
 - THREE PLACE DECIMALS ± 0.005
 - ANGLES $\pm 1^\circ$
 - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.
- FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002
- REMOVE ALL BURRS

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH						MATERIAL			
SPEC No.						SPEC No.			
FIRST USED ON						SCALE			
						2:1			
DATE DRAWN	BY	CHKD	APVD		Switchcraft®				
06-Jun-01	JL	JF	JF						
NAME						PART No.			
EXTENSION JACK						120			
						REV B			

REV	ECO NUMBER	DATE	BY	APVD
B	23532	4-4-01	JL	JF
REVISIONS				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[120](#)