



# NOTES:

1. MATERIALS:  
HANDLE & HOUSING - COPPER ALLOY, NICKEL PLATED  
SPRINGS & GROUND CLIP - SPECIAL COPPER ALLOY  
CLAMP TERMINAL - STEEL, TIN PLATED  
INSULATORS - PHENOLIC & THERMOPLASTIC
2. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING



STAR SYMBOL DENOTES CRITICAL DIMENSION

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES  
-TWO PLACE DECIMALS  $\pm 0.01$   
-THREE PLACE DECIMALS  $\pm 0.005$   
-ANGLES  $\pm 1^\circ$   
-ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN  $\pm 0.002$

3. REMOVE ALL BURRS

DO NOT SCALE DRAWING

SIZE	WIDTH	MULT	LBS/M	TEMPER
------	-------	------	-------	--------

FINISH	MATERIAL
SPEC No.	SPEC No.

FIRST USED ON	SCALE
	2:1

DATE DRAWN	BY	CHKD	APVD
30-Mar-16	TO	TO 3-30-16	TJK 3-30-16

**Switchcraft®**

SHEET	OF
-------	----

NAME	EXTENSION JAX, 3 CONDUCTOR LOCKING, RoHS	PART No.	133	REV	E
------	---	----------	-----	-----	---

E	21962	9-17-97	TO	TJK
REV	ECO NUMBER	DATE	BY	APVD
REVISIONS				

Pro/Engineer CAD File

A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[133](#)