



SPECIFICATIONS:

MATERIAL

- TIP ROD, RING AND HANDLE - BRASS, NICKEL PLATED
- HOUSING AND SLEEVE - ZINC DIE CAST, COPPER AND NICKEL PLATED
- TIP AND RING TERMINALS - BRASS, TIN PLATED
- SLEEVE (CLAMP) TERMINAL - STEEL, TIN PLATED
- INSULATION - THERMOPLASTIC

ELECTRICAL

- DIELECTRIC WITHSTANDING VOLTAGE : 500 VAC
- INSULATION RESISTANCE: 50,000 MEGOHMS MINIMUM (INITIAL)

OPERATING TEMPERATURE

- 20°C TO +65°C

MATING JACK

- TYP, 1/4 INCH, COMMERCIAL TYPE, 3 CONDUCTOR PHONE JACKS

H THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE *	WIDTH *		MULT *		LBS/M *		TEMPER *			
						FINISH *						MATERIAL *				
						SPEC No. *						SPEC No. *				
						FIRST USED ON *				SCALE 2:1		<div>Switchcraft®</div>				
						DATE DRAWN		BY	CHKD		APVD					
H	25760	12-5-07	TJK	TJK	<div>DO NOT SCALE DRAWING</div>	10-28-05		JL	GG		GG		SHEET 1 OF 1			
G	CAD REDRAWN 25124	10-28-05	JL	GG					10-28-05		10-28-05					
REV	ECO NUMBER	DATE	BY	APVD		NAME RA PHONE PLUG, 3 CONDUCTOR. RoHS						PART No. 236				REV H
REVISIONS																

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

236 236PKG