





NOTES:


1. MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, SILVER PLATED

2. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.

3. THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING



SCHEMATIC

PCB LAYOUT
COMPONENT SIDE
TOLERANCE: ±0.002 [±0.05]

REV	ECO NUMBER	DATE	BY	APVD
B	28596	06/07/23	PC	TJK
A	28463	01/31/22	PC	TJK

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]


DO NOT SCALE DRAWING

SolidWorks CAD File

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON			SCALE 6:1		Switchcraft®				
DATE DRAWN	BY	CHKD	APVD						
01/26/22	PC	TJK	TJK	01/26/22		01/26/22		SHEET 1 OF 2	
NAME 3.5 MM PHONE JACK SURFACE MOUNT, RoHS					PART No. 35RASMT2BHSNTRX				REV B


A: CARRIER SIZE

1. DETAIL SIZE REFERENCES: EIA-481
2. SPECIFICATIONS: 24 MM X 12 MM B



B: REEL SIZE

- B 1. QUANTITY: 1000 PCS/REEL
2. MATERIAL: THERMOPLASTIC
3. 13 EMPTY AT START OF REEL AND 22 EMPTY AT END OF REEL



CUSTOMER DRAWING

SCALE 2:1	Switchcraft®	
DATE DRAWN 01/26/22		
DRAWN BY PC	PART No. 35RASMT2BHSNTRX	REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[35RASMT2BHSNTRX](#)