







SCHEMATIC



CUSTOMER DRAWING

NOTES:


1. MATERIALS:
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, GOLD PLATED
2. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.
3. THIS PRODUCT IS RoHS COMPLIANT.

PCB LAYOUT
COMPONENT SIDE

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						SIZE	WIDTH		MULT	LBS/M	TEMPER
						FINISH				MATERIAL	
						SPEC No.				SPEC No.	
						FIRST USED ON			SCALE		Switchcraft®
									6:1		
						DATE DRAWN	BY	CHKD	APVD		
A	28481	03/03/22	PC	TJK	10/27/21	TS	TS	TJK	SHEET 1 OF 2		
					10/27/21			3/1/22			
REV	ECO NUMBER	DATE	BY	APVD	NAME				PART No.		REV
					3.5MM JACK, 4 CONDUCTOR, SURFACE MOUNT, RoHS				35RASMT5CHNTRX		A
REVISIONS					DO NOT SCALE DRAWING						


A: CARRIER SIZE

- 1. DETAIL SIZE REFERENCES: EIA-481
- 2. SPECIFICATIONS: 32 MM X 12 MM
- 3. COVER TAPE: SPECIFICATION ATTACHED (CONDUCTIVE)



B: REEL SIZE

- 1. QUANTITY: 1000 PCS/REEL
- 2. MATERIAL: THERMOPLASTIC



- A: EMPTY 6.30 [160.0] MIN.
- B: EMPTY 3.94 [100.0] MIN.
- C: COVER 15.75 [400.0] MIN.

CUSTOMER DRAWING

SCALE 2:1	Switchcraft®		
DATE DRAWN 3/1/22			
DRAWN BY TJK	PART No. 35RASMT5CHNTRX	SHEET 2 OF 2	
		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

35RASMT5CHNTRX