

NOTES:

1. ALL DIMENSIONS ARE REFERENCE.





2. MATERIALS:

HOUSING: THERMOPLASTIC, BLACK


TERMINALS: COPPER ALLOY, GOLD FLASH

3. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.

4. THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING



SCHEMATIC

PCB LAYOUT
COMPONENT SIDE
TOLERANCE: ±0.002 [±0.05]

REV	ECO NUMBER	DATE	BY	APVD
E	28625	09-28-23	PC	TJK
D	27337	7-30-14	TO	TJK
C	26972	6-20-12	TO	TJK
B	26514	3-25-10	RS	TJK
A	25182	1-13-06	JL	GG

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING



THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH	MATERIAL			
SPEC No.	SPEC No.			
FIRST USED ON		SCALE		
		6:1		
DATE DRAWN	BY	CHKD	APVD	
13-Jan-06	JL	GG	GG	
		1-13-06	1-13-06	
NAME			PART No.	REV
3.5MM PHONE JACK			35RASMT2AHNTRX	E
SURFACE MOUNT, RoHS				

SolidWorks CAD File B

A: CARRIER SIZE


- 1. DETAIL SIZE REFERENCES: EIA-481
- 2. SPECIFICATIONS: 32 MM X 12 MM



CARRIER TAPE

B: REEL SIZE

- 1. QUANTITY: 700 PCS/REEL
- 2. MATERIAL: THERMOPLASTIC
- 3. 8 EMPTY AT START OF REEL



CUSTOMER DRAWING

SCALE NONE	Switchcraft®		
DATE DRAWN 13-Jan-06			
DRAWN BY JL	PART No. 35RASMT2AHNTRX	REV E	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[35RASMT2AHNTRX](#)