

NOTES:

1. ALL DIMENSIONS ARE REFERENCE.





F 2. MATERIALS:

HOUSING - THERMOPLASTIC, BLACK


TERMINALS - COPPER ALLOY, GOLD FLASH

3. SUPPLIED ON TAPE AND REEL, SEE SHEET 2.

4. THIS PRODUCT IS RoHS COMPLIANT.



SCHEMATIC





CUSTOMER DRAWING

PCB LAYOUT
COMPONENT SIDE
TOLERANCE: ±0.002 [±0.05]

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH						MATERIAL					
						SPEC No.						SPEC No.					
						FIRST USED ON				SCALE 6:1		Switchcraft®					
F	28625	09/28/23	PC	TJK		DATE DRAWN 1/13/06	BY JL	CHKD GG 1/13/06		APVD GG 1/13/06							
E	REDRAWN 28478	02/23/22	PC	TJK		DO NOT SCALE DRAWING						SHEET 1 OF 2					
REV	ECO NUMBER	DATE	BY	APVD	NAME 3.5 MM PHONE JACK SURFACE MOUNT, RoHS							PART No. 35RASMT2BHNTRX				REV F	
REVISIONS																	

1. DETAIL SIZE REFERENCES: EIA-481


2. SPECIFICATIONS: 32 MM X 12 MM




1. QUANTITY: 700 PCS/REEL

2. MATERIAL: THERMOPLASTIC

3. 8 EMPTY AT START OF REEL



CUSTOMER DRAWING

SCALE NONE		
DATE DRAWN 1/13/06		
	SHEET 2 OF 2	
DRAWN BY JL	PART No. 35RASMT2BHNTRX	REV F

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[35RASMT2BHNTRX](#)