









46311LDRX




46311LDSRX



46313LDRX






46313LDRSX



RECOMMENDED PANEL CUT-OUT

- NOTES:
- 1. ALL DIMENSIONS REFERENCE UNLESS OTHERWISE SPECIFIED.
 - 2. MATERIALS:
 - HOUSING - CRS, ZINC PLATED
 - BUTTON - THERMOPLASTIC, BLACK
 - SHIMS - THERMOPLASTIC, DARK GRAY
 - DETENT WIRE - MUSIC WIRE
 - TERMINALS & CONTACT SLIDER - COPPER ALLOY, SILVER PLATED
 - TERMINAL BOARD - PHENOLIC
 - 3. SWITCH RATING:
 - 3 AMPS 125 VAC - 0.5 AMPS 125 VDC
 - 4. THIS PRODUCT IS RoHS COMPLIANT.



46313LDRX SHOWN

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
						SIZE	WIDTH		MULT	LBS/M		TEMPER	
						FINISH					MATERIAL		
						SPEC No.					SPEC No.		
						FIRST USED ON			SCALE		Switchcraft®		
							2:1						
A	26002	3/23/06	RS	TJK	DO NOT SCALE DRAWING	DATE DRAWN	BY	CHKD	APVD				
						9/14/09	RS	RS	TJK				
								9/14/09	3/10/11				
REV	ECO NUMBER	DATE	BY	APVD		NAME SLIDE SWITCH 3 POSITION LOCKING, RoHS					PART No. 46300LDRX SERIES		REV A
REVISIONS													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[46313LDR](#) [46311LDRX](#) [46313LDRX](#) [46313LDRSX](#)