



- NOTES:
1. $\varnothing 0.04[1.0\text{mm}] \times 0.09[2.2\text{mm}]$ SLOT IN TERMINALS FOR SOLDERING.
 2. MATERIALS:
HOUSING - DIE CAST ZINC, NICKEL PLATED
INSERT - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, TIN PLATED
 3. THESE PRODUCTS ARE RoHS COMPLIANT.

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
UNLESS OTHERWISE SPECIFIED					SIZE	WIDTH	MULT	LBS/M	TEMPER
1. ALL DIMENSIONS IN INCHES					FINISH			MATERIAL	
- TWO PLACE DECIMALS ± 0.02					SPEC No.			SPEC No.	
- THREE PLACE DECIMALS ± 0.005					FIRST USED ON		SCALE 2:1		
A	26000	3/3/06	TJK	TJK	DATE DRAWN	BY	CHKD TO	APVD TJK	Switchcraft [®]
REV	ECO NUMBER	DATE	BY	APVD	7-22-13	TO	7-22-13	7-23-13	
REVISIONS					NAME FEMALE DIN 3-8 PIN, FLANGE MOUNTED BAYONET LOCKING RECEPTACLE, RoHS				
DO NOT SCALE DRAWING					PART No. 57HB_FX, 60HA_FX, 61HA_FX & 62HB_FX SERIES				
					SHEET 1 OF 1				
					REV A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[62HB7F](#) [62HB8F](#) [60HA4F](#) [61HA5F](#) [57HB5F](#) [57HB3F](#) [57HB3FX](#) [60HA4FX](#) [61HA5FX](#) [62HB7FX](#) [62HB8FX](#)
[57HB5FX](#)