



ST-604
OVERMOLDED 4 PIN FEMALE TINI-QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.



WIRING CHART	
ST-604	WIRE COLOR
PIN 1	BLACK
PIN 2	WHITE
PIN 3	RED
PIN 4	GREEN
SHELL	SHIELD/ DRAINWIRE



NOTES:

1. THIS PRODUCT IS RoHS COMPLIANT

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE	WIDTH		MULT		LBS/M		TEMPER			
						FINISH SPEC No.						MATERIAL SPEC No.				
						FIRST USED ON				SCALE 1.5:1		Switchcraft®				
						DATE DRAWN 7/28/20	BY AB	CHKD AB 7/28/20		APVD TJK 8/10/20						
A	28310	08/25/20	PC	TJK							SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD	NAME CABLE ASSEMBLY, 4 PIN FEMALE TINI QG TO STRIP & TIN					PART No. 604HH__184X				REV A		
REVISIONS					DO NOT SCALE DRAWING											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[604HH079184X](#)