



ST-604
OVERMOLDED 4 PIN FEMALE TINI-QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.



WIRING CHART	
ST-604	WIRE COLOR
PIN 1	BLACK
PIN 2	WHITE
PIN 3	RED
PIN 4	GREEN
SHELL	SHIELD/ DRAINWIRE



NOTES:

1. THIS PRODUCT IS RoHS COMPLIANT

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.								
						SIZE	WIDTH		MULT	LBS/M	TEMPER			
						FINISH SPEC No.				MATERIAL SPEC No.				
						FIRST USED ON			SCALE 1.5:1		<div>Switchcraft®</div>			
						DATE DRAWN	BY	CHKD	APVD					
A	28310	08/25/20	PC	TJK		7/28/20	AB	AB	TJK					
								7/28/20	8/10/20					
REV	ECO NUMBER	DATE	BY	APVD	NAME			CABLE ASSEMBLY, 4 PIN FEMALE TINI QG TO STRIP & TIN			PART No.	604HH__184X		REV
REVISIONS					DO NOT SCALE DRAWING								A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[604HH079184X](#)