




NOTES:

1. MATERIALS:
BODY - BRASS, NICKEL PLATED
CONTACTS - BRASS, NICKEL PLATED
INSULATOR - ABS
HEX NUT - DIE CAST, NICKEL PLATED
2. HEX NUT TO BE SHIPPED ASSEMBLED TO THE BODY OF JACK.
3. THIS PART IS RoHS COMPLIANT.

PART NUMBER	CENTER PIN DIAMETER
721AFMS	0.083 [2.1mm]
712AFMS	0.098 [2.5mm]

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH						MATERIAL			
						SPEC No.						SPEC No.			
						FIRST USED ON				SCALE		Switchcraft®			
								3:1							
A	27939	9/6/17	TJK	TJK	DO NOT SCALE DRAWING	DATE DRAWN	BY	CHKD	APVD	SHEET 1 OF 1					
						8/28/17	TJK	TJK	TJK						
								8/28/17	8/28/17						
REV	ECO NUMBER	DATE	BY	APVD		NAME	FRONT MOUNT SHIELDED POWER JACK, RoHS				PART No. 712AFMS 721AFMS				REV A
REVISIONS															

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

721AFMS 712AFMS