



- NOTES:
- 1. MATERIALS:
TIP, BODY AND COUPLING RING - COPPER ALLOY, NICKEL PLATED
CABLE CLAMP - COPPER ALLOY, TIN PLATED
INSULATION - THERMOPLASTIC, DARK GRAY
HANDLE - ANODIZED ALUMINUM, SEE TABLE FOR COLOR
 - 2. COUPLING RING HAS A #10-48 NS-2B THREAD. 0.050 MINIMUM THREAD PROJECTION OF JACK FOR PROPER LOCK.
 - 3. HANDLE IS SHIPPED UNASSEMBLED.
 - 4. THIS PRODUCT IS RoHS COMPLIANT.

PART NUMBER	HANDLE COLOR
851X	BLACK
856X	RED
881X	CLEAR ANODIZED

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH SPEC No.						MATERIAL SPEC No.					
						FIRST USED ON				SCALE 6:1		Switchcraft®					
						DATE DRAWN	BY	CHKD		APVD							
B	27510	06-03-15	TJK	TJK		01-23-08	AH	AH		TJK		SHEET 1 OF 1					
A	26062	06-28-06	TO	TJK		01-23-08 01-23-08											
REV	ECO NUMBER	DATE	BY	APVD	NAME 2 CONDUCTOR, LOCKING MICRO-PLUG ASSEMBLY, RoHS						PART No. 851X, 856X, 881X				REV B		
REVISIONS					DO NOT SCALE DRAWING												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[851](#) [881](#) [851X](#) [881X](#) [856](#) [883](#) [2P1419](#) [2P1503A](#) [2P1495](#) [856X](#)