



DB25F PIN-OUT VIEW

DB25F AND XLRM AND XLRF WIRING CHART					
XLR (CHANNEL)	XLR (DESC.)	CABLE (COLOR)	PIN 2 (RED)	PIN 3 (BLACK)	PIN 1 (BARE)
1	XLRF	BROWN	24	12	25
2	XLRF	RED	10	23	11
3	XLRF	ORANGE	21	9	22
4	XLRF	YELLOW	7	20	8
5	XLRM	GREEN	18	6	19
6	XLRM	BLUE	4	17	5
7	XLRM	PURPLE	15	3	16
8	XLRM	GRAY	1	14	2

NOTES:

1. BREAKOUT CABLE LENGTH: 18 +/- 0.75 INCHES. SEE TABLE FOR COLOR.

B 2. THIS PRODUCT COMES COILED AND PACKAGED IN BAG.

B 3. MATERIALS:
XLR CONNECTORS:
HANDLE - ZINC ALLOY, NICKEL PLATED
HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
INSULATOR - THERMOPLASTIC, GREEN
SOCKET CONTACTS AND PINS - SPECIAL COPPER ALLOY, SILVER PLATED
H.S. TUBING - THERMOPLASTIC
DSUB:
CABLE CLAMP - COPPER, NICKEL PLATED
SHELL - STEEL, TIN PLATED
INSULATORS - THERMOPLASTIC
SCREW LOCKS - BRASS, NICKEL PLATED

4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE	WIDTH		MULT		LBS/M		TEMPER			
						FINISH						MATERIAL				
						SPEC No.						SPEC No.				
C	27520	06/08/15	PC	TJK		FIRST USED ON				SCALE 1:2		<div>Switchcraft®</div> <div>SHEET 1 OF 1</div>				
B	26637	10/4/10	RS	TJK		DATE DRAWN	BY	CHKD		APVD						
A	26568	7/20/10	RS	TJK		7/15/09	JGK	RS 12/1/10		TJK 12/1/10						
						NAME						PART No.				REV
REV	ECO NUMBER	DATE	BY	APVD		DB25F TO 4-XLRM & 4-XLRF, RoHS						DB25FXLRMXMLRF				C
REVISIONS						DO NOT SCALE DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25FXLRMXLRF](#)