



DB25F AND XLRM WIRING CHART					
XLR (CHANNEL)	XLR (DESC.)	CABLE (COLOR)	PIN 2 (RED)	PIN 3 (BLACK)	PIN 1 (BARE)
1	XLRM	BROWN	24	12	25
2	XLRM	RED	10	23	11
3	XLRM	ORANGE	21	9	22
4	XLRM	YELLOW	7	20	8
5	XLRM	GREEN	18	6	19
6	XLRM	BLUE	4	17	5
7	XLRM	PURPLE	15	3	16
8	XLRM	GRAY	1	14	2

- NOTES:
- BREAKOUT CABLE LENGTH: 18 +/- 0.75 INCHES. SEE TABLE FOR COLOR.
 - THIS PRODUCT COMES COILED AND PACKAGED IN BAG.
 - MATERIALS:
 - XLR CONNECTORS:
 - HANDLE - ZINC ALLOY, NICKEL PLATED
 - HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
 - INSULATOR - THERMOPLASTIC, GREEN
 - PINS - SPECIAL COPPER ALLOY, SILVER PLATED
 - H.S. TUBING - THERMOPLASTIC
 - DSUB:
 - CABLE CLAMP - COPPER, NICKEL PLATED
 - SHELL - STEEL, TIN PLATED
 - INSULATORS - THERMOPLASTIC
 - SCREW LOCKS - BRASS, NICKEL PLATED
 - THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH					MATERIAL									
						SPEC No.					SPEC No.									
C	27520	06/08/15	PC	TJK		FIRST USED ON				SCALE 1:2		<div>Switchcraft®</div>								
B	26637	10/4/10	RS	TJK		DATE DRAWN	BY	CHKD	APVD											
A	26568	7/20/10	RS	TJK		7/16/09	JGK	RS	TJK											
							11/30/10	11/30/10		SHEET 1 OF 1										
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.					REV					
REVISIONS					DO NOT SCALE DRAWING					DB25F TO 8-XLRM, RoHS					DB25FXLRM					C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25FXLRM](#)