


DB25 AND TRS WIRING CHART				
JACK (CHANNEL)	CABLE (COLOR)	TIP OR RING (RED)	SLEEVE (BLACK)	SLEEVE (BARE)
1	BROWN	24	12	25
2	RED	10	23	11
3	ORANGE	21	9	22
4	YELLOW	7	20	8
5	GREEN	18	6	19
6	BLUE	4	17	5
7	PURPLE	15	3	16
8	GRAY	1	14	2



DB25 PIN-OUT VIEW

PART NUMBER	CABLE LENGTH "X"
DB25MM10TRS	10.00 FT +/- 1.50 IN
DB25MM12TRS	12.00 FT +/- 1.50 IN
DB25MM15TRS	15.00 FT +/- 2.00 IN

- NOTES:
- BREAKOUT CABLE LENGTH: 18.00 +/- 0.75 INCHES.
 - THE PRODUCT COMES COILED AND PACKAGED IN A BAG.
 - JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (4) AND #M3 THREAD (4) JACK SCREWS.
 - MATERIALS:
TRS PLUG AND HANDLE - COPPER ALLOY, NICKEL PLATED
H.S. TUBING - THERMOPLASTIC
DSUB: CABLE CLAMPS - COPPER, NICKEL PLATED
SHELL - STEEL, TIN PLATED
INSULATORS - THERMOPLASTIC
JACKSCREWS - STAINLESS STEEL
 - THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.																
						SIZE	WIDTH		MULT		LBS/M		TEMPER									
						FINISH SPEC No.						MATERIAL SPEC No.										
D	26795	7-8-11	TO	TJK		FIRST USED ON				SCALE 2:1		Switchcraft®										
C	26757	04/06/11	BL	JEB		DATE DRAWN	BY	CHKD		APVD												
B	26637	10/11/10	RS	TJK		02/22/08	JGK	RS		TJK		SHEET 1 OF 1										
A	25959	10/6/08	RS	TJK																		
REV	ECO NUMBER	DATE	BY	APVD		NAME						PART No.				REV						
REVISIONS						DO NOT SCALE DRAWING					DB25M INSERT CABLE, RoHS						DB25MM__TRS				D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25MM10TRS](#)