



DB25 PIN-OUT VIEW FOR DB25

DB25 AND 297 WIRING CHART				
JACK (CHANNEL)	CABLE (COLOR)	TIP (RED)	RING (BLACK)	SLEEVE (BARE)
1	BROWN	24	12	25
2	RED	10	23	11
3	ORANGE	21	9	22
4	YELLOW	7	20	8
5	GREEN	18	6	19
6	BLUE	4	17	5
7	PURPLE	15	3	16
8	GRAY	1	14	2

NOTES:

- BREAKOUT CABLE LENGTH: 18.00 +/- 0.75 INCHES.
- THE PRODUCT COMES COILED AND PACKAGED IN A BAG.
- JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (2) AND #M3 THREAD (2) JACKSCREWS.
- MATERIALS:
LITTEL PLUG:
SLEEVE, TIP AND BODY - COPPER ALLOY, NICKEL PLATED
TERMINALS - SPECIAL COPPER ALLOY
HANDLE - COPPER ALLOY, NICKEL PLATED
DSUB - COPPER ALLOY, NICKEL PLATED WITH GOLD PINS
CABLE - COPPER, THERMOPLASTIC
JACKSCREWS - STAINLESS STEEL
- THIS PRODUCT IS RoHS COMPLIANT.

PART NO	CABLE LENGTH "X"
DB25M02TRS	2.00 FT +/- 1.50 IN
DB25M10TRS	10.00 FT +/- 1.50 IN

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH SPEC No.						MATERIAL SPEC No.								
D	26795	7-8-11	TO	TJK		FIRST USED ON				SCALE 1:2		Switchcraft®								
C	26637	10/4/10	RS	TJK		DATE DRAWN		BY	CHKD		APVD									
B	25926	8/14/08	JGK	TJK		9/12/06		JGK	RS 11/24/10		TJK 11/24/10									
A	25716	10/03/07	JGK	TJK		NAME						PART No.				REV				
REV	ECO NUMBER	DATE	BY	APVD		DO NOT SCALE DRAWING						DB25M TO 8 TRS PLUGS, RoHS				DB25M__TRS				D
REVISIONS																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25M10TRS](#)