



DB25 AND XLR FEMALE WIRING CHART				
XLR (CHANNEL)	CABLE (COLOR)	PIN 2 (RED)	PIN 3 (BLACK)	PIN 1 (BARE)
1	BROWN	24	12	25
2	RED	10	23	11
3	ORANGE	21	9	22
4	YELLOW	7	20	8
5	GREEN	18	6	19
6	BLUE	4	17	5
7	PURPLE	15	3	16
8	GRAY	1	14	2

PART NO.	CABLE LENGTH "X"
DB25M02XLRF	2.00 FT +/- 1.50 IN
DB25M03XLRF	3.00 FT +/- 1.50 IN
DB25M10XLRF	10.00 FT +/- 1.50 IN

NOTES:

- BREAKOUT CABLE LENGTH: 18.00 +/- 0.75 INCHES. SEE TABLE FOR COLOR.
- THIS PRODUCT COMES COILED AND PACKAGED IN BAG.
- JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (2) AND #M3 THREAD (2) JACKSCREWS.
- MATERIALS:
XLR FEMALE CONNECTOR:
HANDLE - ZINC ALLOY, NICKEL PLATED
HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
INSULATOR - THERMOPLASTIC, GREEN
SOCKET CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
H.S. TUBING - THERMOPLASTIC
DSUB - COPPER ALLOY, NICKEL PLATED WITH GOLD PINS
JACKSCREWS - STAINLESS STEEL
- THIS PRODUCT IS RoHS COMPLIANT.

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH SPEC No.						MATERIAL SPEC No.								
D	26795	7-8-11	TO	TJK		FIRST USED ON				SCALE 2:1		Switchcraft®								
C	26637	10/11/10	RS	TJK		DATE DRAWN		BY	CHKD		APVD									
B	25891	9/9/08	SRC	TJK		9/12/06		JGK	RS 11/8/10		TJK 11/9/10									
A	25716	10/03/07	JGK	TJK		NAME DB25M TO 8 FEMALE XLR, RoHS							PART No.		REV					
													SHEET 1 OF 1				DB25M_XLRF		D	
REV	ECO NUMBER	DATE	BY	APVD																
REVISIONS						DO NOT SCALE DRAWING														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25M10XLRF](#)