



DB25 AND XLR F AND XLR M WIRING CHART					
XLR (CHANNEL)	XLR (DESC.)	CABLE (COLOR)	PIN 2 (RED)	PIN 3 (BLACK)	PIN 1 (BARE)
1	XLRF	BROWN	24	12	25
2	XLRF	RED	10	23	11
3	XLRF	ORANGE	21	9	22
4	XLRF	YELLOW	7	20	8
5	XLRM	GREEN	18	6	19
6	XLRM	BLUE	4	17	5
7	XLRM	PURPLE	15	3	16
8	XLRM	GRAY	1	14	2

PART NUMBER	CABLE LENGTH "X"
DB25M02XLRMXLRF	2.00 FT +/- 1.50 IN
DB25M10XLRMXLRF	10.00 FT +/- 1.50 IN

- NOTES:
- BREAKOUT CABLE LENGTH: 18.00 +/- 0.75 INCHES. SEE TABLE FOR COLOR.
 - THIS PRODUCT COMES COILED AND PACKAGED IN BAG.
 - JACKSCREWS ARE SHIPPED UNASSEMBLED. CABLE COMES WITH BOTH #4-40 THREAD (2) AND #M3 THREAD (2) JACKSCREWS.
 - MATERIALS:
XLR CONNECTORS:
HANDLE - ZINC ALLOY, NICKEL PLATED
HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
INSULATOR - THERMOPLASTIC, GREEN
CONTACTS AND PINS - SPECIAL COPPER ALLOY, SILVER PLATED
H.S. TUBING - THERMOPLASTIC
DSUB - COPPER ALLOY, NICKEL PLATED WITH GOLD PINS
JACKSCREWS - STAINLESS STEEL
 - THIS PRODUCT IS RoHS COMPLIANT.

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH SPEC No.						MATERIAL SPEC No.								
D	26795	7-8-11	TO	TJK		FIRST USED ON						SCALE 1:2		<div>Switchcraft®</div>						
C	26637	10/11/10	RS	TJK		DATE DRAWN		BY	CHKD		APVD									
B	25891	9/9/08	SRC	TJK		9/12/06		JGK	RS		TJK									
A	25716	10/03/07	JGK	TJK					11/10/10		11/10/10									
REV	ECO NUMBER	DATE	BY	APVD	NAME						PART No.				REV					
REVISIONS					DO NOT SCALE DRAWING					DB25M TO 4 XLRF & 4 XLRM, RoHS						DB25M_ _XLRMXLRF				D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DB25M10XLRMXLRF](#)