











RECOMMENDED
FRONT MOUNTING CUT-OUT





RECOMMENDED
REAR MOUNTING CUT-OUT



NOTES:

- 1. AGENCY IDENTIFICATION & RATING:
UL & CSA: 15A 250V~
- 2. MEETS IEC 60320 SPECIFICATION
- 3. MATERIALS:
HOUSING: BLACK POLYESTER
TERMINALS: TIN PLATED COPPER ALLOY
CONTACT PINS: TIN PLATED COPPER ALLOY
- 4. THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING

REV	ECO NUMBER	DATE	BY	APVD
C	28549	01/16/23	PC	TJK
B	28175	6/4/19	TJK	TJK
A	26895	12/16/11	BL	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED				
1. ALL DIMENSIONS IN INCHES [mm]				
- TWO PLACE DECIMALS ±0.02 [0.5]				
- THREE PLACE DECIMALS ±0.005 [0.13]				
DO NOT SCALE DRAWING				

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON			SCALE 2:1		Switchcraft®				
DATE DRAWN	BY	CHKD	APVD						
11/17/11	BL	BL	TJK	11/17/11		SHEET 1		OF 1	
NAME MALE AC RECEPTACLE 0.25 FAST-ON TERMINALS, RoHS					PART No. EAC311X				REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[EAC311X](#)