




NOTES:



- 1. MEETS IEC 60320 SPECIFICATION.
- 2. AGENCY APPROVAL & RATING:
VDE: 10A, 250V AC.
UL & CSA: 15A, 250V~ AC
- 3. MATERIALS:
HOUSING AND COVER, BLACK THERMOPLASTIC.
TERMINALS, TIN PLATED COPPER ALLOY.
- 4. THIS PRODUCT IS RoHS COMPLIANT.

M	28549	01/16/23	PC	TJK	
L	26887	11/29/11	BL	TJK	
K	24129	03/27/02	BL	TJK	
REV	ECO NUMBER	DATE	BY	APVD	
REVISIONS					

UNLESS OTHERWISE SPECIFIED					
1. ALL DIMENSIONS IN INCHES [mm]					
- TWO PLACE DECIMALS ±0.02 [0.5]					
- THREE PLACE DECIMALS ±0.005 [0.13]					
DO NOT SCALE DRAWING					

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH					MATERIAL				
SPEC No.					SPEC No.				
FIRST USED ON				SCALE		Switchcraft®			
				3:1					
DATE DRAWN	BY	CHKD		APVD					
05/05/89	TJK	GHJ		RV					
		05/09/89		05/09/89					
NAME MALE AC RECEPTACLE						PART No.		REV	
RIGHT ANGLE PC MOUNT, RoHS						EAC333		M	

CUSTOMER DRAWING



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[EAC333](#)