



NOTES:

- SWITCH SPECIFICATIONS:
SPDT MOMENTARY PUSH-BUTTON SWITCH
RATING: 250mA @ 48VDC.
TERMINAL STYLE: SOLDER TERNINALS, SILVER PLATED

- MATERIALS:
FLANGE - ZINC, SEE TABLE FOR FINISH
SWITCH BODY, MOUNTING HARDWARE - COPPER ALLOY, NICKEL PLATED.
SWITCH PUSHBUTTON - RED OR BLACK THERMOPLASTIC SEE TABLE
SWITCH INSULATOR - PHENOLIC
SWITCH TERMINALS & CONTACTS - COPPER ALLOY, AND/OR COPPER ALLOY SILVER PLATED

- FOR FLANGE MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY, ADD THE SUFFIX "PKG" TO THE PART NUMBER.

- THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	ACTUATOR COLOR	FLANGE FINISH
EHPBSMR	RED	NICKEL
EHPBSMRB	RED	BLACK
EHPBSMB	BLACK	NICKEL
EHPBSMBB	BLACK	BLACK

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH					MATERIAL	
						SPEC No.					SPEC No.	
						FIRST USED ON			SCALE		<div>Switchcraft®</div> <div>SHEET 1 OF 1</div>	
						*			2:1			
						DATE DRAWN	BY	CHKD	APVD			
A	26781	6-9-11	TO	TJK		07/28/09	BS	PNK	SRC			
								01/31/11	01/31/11			
REV	ECO NUMBER	DATE	BY	APVD		NAME EH SERIES SPDT PUSHBUTTON SWITCH, RoHS					PART No.	REV
REVISIONS					DO NOT SCALE DRAWING					EHPBSM SERIES		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EHPBSMB](#) [EHPBSMBB](#) [EHPBSMR](#) [EHPBSMRB](#) [EHPBSMBBPKG](#) [EHPBSMBPKG](#) [EHPBSMRPKG](#)