




NOTES:

1. IP67 RATED WHEN PROPERLY ASSEMBLED.

A 2. CABLE RANGE: Ø 0.177 - 0.236 [4.5 - 6.0].

3. ALL PARTS SHIPPED ASSEMBLED.


4. MATERIALS:

RJ45 PLUG - CAT6 SHIELDED PLUG

GASKET AND SEAL RING - BLACK, EPDM RUBBER

CLAMP RING, SCREW NUT, SEAL NUT- BLACK, THERMOPLASTIC

5. THIS PRODUCT IS RoHS COMPLIANT



CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
						SIZE	WIDTH	MULT	LBS/M	TEMPER	
						FINISH			MATERIAL		
						SPEC No.			SPEC No.		
						FIRST USED ON		SCALE		Switchcraft®	
								1.5:1			
A	28311	08/24/20	PC	TJK		DATE DRAWN	BY	CHKD	APVD		
					7/7/20	FM	FM	TJK			
							7/7/20	7/17/20			
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.	REV
					SEALED RJ45 CAT6 SHIELDED PLUG, CABLE RANGE Ø 4.5 - 6.0mm					ENDC6S	A

DO NOT SCALE DRAWING

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDC6S](#)