











- NOTES:
1. IP67 RATED WHEN PROPERLY ASSEMBLED.
 2. ALL PARTS SHIPPED ASSEMBLED.
 3. PANEL THICKNESS MAX OF 0.138 [3.50].
 4. MATERIALS:
RJ45 JACK: CAT5E STP
HOUSING, HEX NUT - BLACK THERMOPLASTIC
GROUND TERMINAL: NICKEL PLATED, PHOSPHER BRONZE
GASKET - BLACK, EPDM RUBBER
 5. THIS PRODUCT IS RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE	WIDTH		MULT		LBS/M		TEMPER			
						FINISH						MATERIAL				
						SPEC No.						SPEC No.				
						FIRST USED ON				SCALE 2:1		Switchcraft®				
						DATE DRAWN	BY	CHKD		APVD						
A	28311	08/24/20	PC	TJK		6/23/20	FM	FM 6/23/20		TJK 7/21/20						
REV	ECO NUMBER	DATE	BY	APVD		NAME RJ45 CAT 5E						PART No.				REV
						PANEL MOUNT FEED-THRU JACK						ENDP5EF				A
REVISIONS						DO NOT SCALE DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDP5EF](#)