



- NOTES:
1. IP67 RATED WHEN PROPERLY ASSEMBLED.
 2. PANEL THICKNESS MAX OF 0.169 [4.30].
 3. ALL PARTS SHIPPED ASSEMBLED.
 4. MATERIALS:
HOUSING AND HEX NUT - NICKEL PLATED, ZINC ALLOY
SPRING WASHER - STAINLESS STEEL
GASKET - SILICONE, BLACK
 5. THIS PRODUCT IS RoHS COMPLIANT.

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH						MATERIAL								
						SPEC No.						SPEC No.								
						FIRST USED ON				SCALE		<div>Switchcraft®</div>								
						DATE DRAWN		BY	CHKD		APVD									
						7/7/20		FM	FM		TJK									
									7/7/20		7/30/20									
B	28436	11/01/21	PC	TJK	<div>DO NOT SCALE DRAWING</div>	NAME RJ45 CAT6 PANEL MOUNT, SHIELDED JACK, PC TERMINALS											PART No.		REV	
A	28311	08/24/20	PC	TJK		ENDP6SPC											B			
REV	ECO NUMBER	DATE	BY	APVD																
REVISIONS																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDP6SPC](#)