




NOTES:
1. IP67 RATED WHEN PROPERLY ASSEMBLED.
2. PANEL THICKNESS MAX OF 0.169 [4.30].
3. ALL PARTS SHIPPED ASSEMBLED.
4. MATERIALS:
HOUSING AND HEX NUT - NICKEL PLATED, ZINC ALLOY
SPRING WASHER - STAINLESS STEEL
GASKET - SILICONE, BLACK
5. THIS PRODUCT IS RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH				MATERIAL		
						SPEC No.				SPEC No.		
						FIRST USED ON			SCALE		Switchcraft®	
						DATE DRAWN	BY	CHKD	APVD			
						7/7/20	FM	FM	TJK			
B	28436	11/01/21	PC	TJK			7/7/20	7/30/20				
A	28311	08/24/20	PC	TJK								
REV	ECO NUMBER	DATE	BY	APVD		NAME RJ45 CAT6 PANEL MOUNT, SHIELDED JACK, PC TERMINALS				PART No.	REV	
REVISIONS					DO NOT SCALE DRAWING					ENDP6SPC	B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDP6SPC](#)