






NOTES:

1. CAP FOR ENDP5EF, ENDP6PC AND ENDP6SPC.
2. IP67 RATED WHEN PROPERLY ASSEMBLED.
3. ALL PARTS SHIPPED ASSEMBLED.
4. MAX PANEL THICKNESS OF 0.110 [2.8].
5. MATERIALS:
SCREW NUT - BLACK, THERMOPLASTIC
STRAP - BLACK, THERMOPLASTIC RUBBER
SCREW- STAINLESS STEEL
GASKET- BLACK, EPDM RUBBER
6. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH						MATERIAL			
						SPEC No.						SPEC No.			
						FIRST USED ON				SCALE		Switchcraft®			
								1:1							
A	28311	08/24/20	PC	TJK		DATE DRAWN	BY	CHKD	APVD		SHEET 1 OF 1				
					7/9/20	FM	FM	TJK							
								7/9/20	7/17/20						
REV	ECO NUMBER	DATE	BY	APVD		NAME WATERPROOF						PART No.		REV	
					DO NOT SCALE DRAWING	SCREW CAP, THREADED						ENDPCAP		A	

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ENDPCAP](#)