









RECOMMENDED
CABLE STRIPPING DIMENSIONS
SWITCHCRAFT STRIPPING TOOL #PTS1



NOTES:

FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER 00-8-626
2. BRASS PER 00-8-613
3. NICKEL PLATING 100 MIN THICK OVER COPPER STRIKE.
4. NICKEL PLATING 200 MIN THICK OVER COPPER STRIKE.
5. GOLD PLATING 3 MIN THICK OVER NICKEL PLATING 100 MIN THICK OVER COPPER STRIKE.
6. TEFLON MIL-P-19468
7. JIS H 3250, C 2700
8. CRIMPED FERRULE HEX CRIMP SIZE 0.255
9. CRIMPED CONTACT PIN SQUARE SQUARE CRIMP SIZE 0.042
10. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
11. THIS PRODUCT IS RoHS COMPLIANT.

					☆ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH					MATERIAL				
						SPEC No.					SPEC No.				
						FIRST USED ON				SCALE 3:1		Switchcraft®			
B	26364	10-31-06	RS	TJK	DATE DRAWN	BY	CHKD	APVD							
A	26142	10-31-06	RF	TJK	10-31-06	RF	RF	TJK							
							10-31-06	10-31-06		SHEET 1 OF 1					
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.					REV
					75 OHM BNC CONNECTOR 8241 CABLE, RoHS					HP75BNC1X					B
REVISIONS					DO NOT SCALE DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[HP75BNC1X](#)