




**NOTES:**  
1. SPECIFICATIONS:  
**ELECTRICAL:**  
MEETS SMPTE 2082-1  
CHARACTERISTIC IMPEDANCE: 75 OHMS  
CONTACT RESISTANCE: LESS THAN 50 MILLIOHMS  
**INTERFACE:**  
RECOMMENDED SWITCHCRAFT MICRO PLUGS  
TO MEET SMPTE 2082-1  
**FRONT INTERFACE:**  
PATCHCORDS VMMP\_05UHD  
PATCHCORDS VMMP\_55UHD  
LOOPING PLUG VMMLPUHD  
DUAL TERMINATED PLUG VMMTPUHD  
SINGLE TERMINATED PLUG VMMSTPUHD  
**REAR INTERFACE PORT:**  
MATES WITH SWITCHCRAFT MICRO BNC UHDMB55 AND UHDMB05.  
**MECHANICAL:**  
VIBRATION: PER MIL - STD 202, METHOD 201  
**MATERIAL:**  
CHANNEL - ALUMINUM ALLOY, ANODIZED BRIGHT BLUE PEWTER  
INSERT - THERMOPLASTIC, BLACK  
MARKING STRIPS - THERMOPLASTIC, WHITE  
MARKING STRIP COVERS - THERMOPLASTIC, CLEAR  
PLASTIC PINS, JACK MTG. SCREWS - THERMOPLASTIC, NATURAL (WHITE)  
JACK HOUSING: COPPER ALLOY, NICKEL PLATED  
JACK CENTER CONTACTS: SPECIAL COPPER ALLOY, GOLD PLATED  
JACK GROUND SPRINGS: STAINLESS STEEL  
JACK INSULATOR: TEFLON  
CABLE SUPPORT - STEEL, BLACK EPOXY  
PATCHBAY MOUNTING SCREWS - STEEL, NICKEL PLATED.

2. K629N HARDWARE KIT (4 x #10-32 MOUNTING SCREWS) SHIPPED UNASSEMBLED WITH EACH PATCHBAY.

3. THIS PRODUCT IS RoHS COMPLIANT.

|           |            |          |    |      |               |                                                                                                                                                                                            |     |          |                                    |                         |          |                |     |
|-----------|------------|----------|----|------|---------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|----------|------------------------------------|-------------------------|----------|----------------|-----|
|           |            |          |    |      |               | THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY. |     |          |                                    |                         |          |                |     |
|           |            |          |    |      |               | UNLESS OTHERWISE SPECIFIED                                                                                                                                                                 |     | SIZE     | WIDTH                              | MULT                    | LBS/M    | TEMPER         |     |
|           |            |          |    |      |               | 1. ALL DIMENSIONS IN INCHES [mm]<br><br>- TWO PLACE DECIMALS    ±0.02 [0.5]<br><br>- THREE PLACE DECIMALS    ±0.005 [0.13]                                                                 |     | FINISH   |                                    |                         | MATERIAL |                |     |
|           |            |          |    |      | SPEC No.      |                                                                                                                                                                                            |     | SPEC No. |                                    |                         |          |                |     |
|           |            |          |    |      | FIRST USED ON |                                                                                                                                                                                            |     | SCALE    |                                    | <div>Switchcraft®</div> |          |                |     |
|           |            |          |    |      |               |                                                                                                                                                                                            |     | 1.5:2    |                                    |                         |          |                |     |
|           |            |          |    |      | DATE DRAWN    |                                                                                                                                                                                            |     | BY       | CHKD                               |                         |          | APVD           |     |
| A         | 28340      | 12/07/20 | PC | TJK  |               | 7/18/19                                                                                                                                                                                    | PNK | 7/18/19  | 7/18/19                            | SHEET    1    OF    1   |          |                |     |
| REV       | ECO NUMBER | DATE     | BY | APVD |               | NAME                                                                                                                                                                                       |     |          | PATCHBAY, 48 X 2 UHD               |                         |          | PART No.       | REV |
| REVISIONS |            |          |    |      |               | DO NOT SCALE DRAWING                                                                                                                                                                       |     |          | MICRO SINGLE VIDEO JACK, BNC, RoHS |                         |          | MMVPSMB48K1UHD | A   |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

MMVPSMB48K1UHD