










P3907





PART NUMBER	GROMMET SIZE	I.D. SIZE REF	CABLE O.D. RANGE
P3907	A	0.500 [12.7]	0.375 - 0.500 [9.5 - 12.7]
P3908	B	0.600 [15.2]	0.500 - 0.600 [12.7 - 15.2]
P3909	C	0.700 [17.8]	0.600 - 0.700 [15.2 - 17.8]



P3908



P3909



CUSTOMER DRAWING

- NOTES:
- 1. MATERIAL: THERMOPLASTIC ELASTOMER, BLACK.
 - 2. DIMENSIONS SHOWN FOR REFERENCE ONLY.
 - 3. THIS PART IS RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE	WIDTH		MULT		LBS/M		TEMPER			
						FINISH SPEC No.						MATERIAL (SEE NOTES) SPEC No.				
						FIRST USED ON EP7 SERIES				SCALE 1.5:1		Switchcraft®				
A	28688	6/11/24	PC	TJK		DATE DRAWN 6/11/24	BY PNK	CHKD PNK 6/11/24		APVD SRC 6/11/24						
REV	ECO NUMBER	DATE	BY	APVD		NAME GROMMETS EP7 SERIES, RoHS						PART No. P3907 - P3909				REV A
REVISIONS					DO NOT SCALE DRAWING					SHEET 1 OF 1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[P3907](#) [P3909](#) [P3908](#)