


- NOTES:
- HEX NUT, FLAT WASHER, AND PANEL O-RING SUPPLIED UNASSEMBLED
  - DIMENSIONS SHOWN FOR REFERENCE ONLY.
  - MATERIAL:**  
HOUSINGS, HEX NUT - COPPER ALLOY, NICKEL PLATED  
INSULATOR HOUSING - THERMOPLASTIC, BEIGE  
O-RINGS - THERMOPLASTIC RUBBER, LUBRICATED WITH SYNTHETIC GREASE  
TERMINAL INSULATORS - PHENOLIC  
FLAT WASHER - COPPER ALLOY, NICKEL PLATED  
PIN, SPRING, TERMINALS - COPPER ALLOY, SILVER PLATED
  - IT IS RECOMMENDED THAT THE JACK MOUNTING NUT BE TIGHTENED SNUG BY HAND BEFORE APPLYING A FINAL TIGHTENING TORQUE OF 8-10 LB-IN USING HAND TOOLS ONLY. POWER DRIVER OR IMPACT DRIVERS ARE NOT RECOMMENDED.
  - THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER	CENTER PIN Ø (JACK SIZE)	MATING POWER PLUG
PCL712ASH	0.10 (2.5 mm)	761KSH12, 761KSH15, 761KSH17
PCL722ASH	0.080 (2.0 mm)	S761KSH12, S761KSH15, S761KSH17



					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
						SIZE	WIDTH		MULT	LBS/M	TEMPER		
						FINISH SPEC No.					MATERIAL SPEC No.		
D	28397	06/11/21	PC	TJK		FIRST USED ON			SCALE 2:1		Switchcraft®		
C	28350	12/22/20	PC	TJK		DATE DRAWN	BY	CHKD	APVD				
B	28079	09/20/18	PC	TJK		6/28/16	PNK	PNK 6/28/16	SRC 6/28/16				
A	27941	09/06/17	PC	TJK		NAME SEALED HT POWER JACKS STRAIGHT PC, RoHS					PART No. PCL712ASH, PCL722ASH		REV D
REV	ECO NUMBER	DATE	BY	APVD									
REVISIONS					DO NOT SCALE DRAWING								

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[PCL722ASH](#) [PCL712ASH](#)