








CUSTOMER DRAWING

NOTES:

1. MATERIALS:

HOUSING - THERMOPLASTIC, BLACK
SHELL - STEEL, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL

2. ELECTRICAL CHARACTERISTICS:

CONTACT RESISTANCE - 30m OHMS MAX
INSULATION RESISTANCE - 1000M OHMS MIN @ 100V DC
CURRENT RATING - 1AMP MAX
DIELECTRIC WITHSTAND VOLTAGE - 500V AC FOR 1 MINUTE

3. PART IS RoHS COMPLIANT.

A	28548	10/26/22	PC	TJK
REV	ECO NUMBER	DATE	BY	APVD
REVISIONS				

UNLESS OTHERWISE SPECIFIED

- ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ± 0.02 [0.5]
- THREE PLACE DECIMALS ± 0.008 [0.20]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON			SCALE 4:1		Switchcraft®				
DATE DRAWN	BY	CHKD	APVD						
8/25/22	MK	MK	MK		SHEET 1 OF 1				
NAME VERTICAL USB TYPE-A 2.0, RoHS					PART No. PCUA20E			REV A	

SolidWorks CAD File B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[PCUA20E](#)