








NOTES:

1. MATERIALS:

HOUSING - THERMOPLASTIC, BLUE
SHELL - STEEL, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL

2. ELECTRICAL CHARACTERISTICS:

CONTACT RESISTANCE - 30m OHMS MAX
INSULATION RESISTANCE - 1000M OHMS MIN @ 500V DC
CURRENT RATING - 1.5A MAX
DIELECTRIC WITHSTANDING - 500V AC FOR 1 MINUTE

3. OPERATION TEMPERATURE - -30°C TO +85°C

4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.008 [0.20]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.										
						SIZE	WIDTH		MULT		LBS/M		TEMPER			
						FINISH SPEC No.						MATERIAL SPEC No.				
						FIRST USED ON				SCALE 4:1		Switchcraft®				
						DATE DRAWN	BY	CHKD		APVD						
A	28548	10/26/22	PC	TJK		8/30/22	MK	MK 10/19/22		MK 10/19/22		SHEET 1 OF 1				
REV	ECO NUMBER	DATE	BY	APVD	NAME				VERTICAL USB TYPE-A 3.0, RoHS				PART No.		REV	
REVISIONS					DO NOT SCALE DRAWING					PCUA30E				A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[PCUA30E](#)