



NOTES:

1. DIMENSIONS IN MILLIMETERS [INCHES].
2. TAPE CONFORMS TO ANSI/EIA-481.
3. MAXIMUM COMPONENT ROTATION WITHIN CAVITY 20°.
4. REEL SIZE 22 INCH., PLASTIC.
5. PART QUANTITY PER REEL: 375.
6. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
7. THIS PRODUCT IS RoHS COMPLIANT

PART NUMBER	PART REV.	POWER JACK
RASH712PTRP22X	A	RASH712PX
RASH722PTRP22X	A	RASH722PX
RASH732PTRP22X	A	RASH732PX

CUSTOMER DRAWING

					<div>★ STAR SYMBOL DENOTES CRITICAL DIMENSION</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.</div> <div>2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002</div> <div>3. REMOVE ALL BURRS</div>	SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH				MATERIAL					
						SPEC No.				SPEC No.					
						FIRST USED ON			SCALE			<div>Switchcraft®</div>			
						3:2									
A	27833	1/17/17	TJK	TJK		DATE DRAWN	BY	CHKD	APVD						
						12-Feb-19	TJK	TJK	TJK						
								2/12/19	2/12/19						
REV	ECO NUMBER	DATE	BY	APVD		NAME				PART No.				REV	
REVISIONS					DO NOT SCALE DRAWING	RASH POWER JACK W/POST TAPE & REEL 22", RoHS				RASH7_2PTRP22X				A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[RASH722TRP22X](#) [RASH712PTRP22X](#) [RASH732TRP22X](#) [RASH712TRP22X](#)