




- NOTES:
- PARTS ARE SUPPLIED ON TAPE AND REEL.
REEL SIZE ϕ 13.0 [330] PLASTIC, 110 PARTS PER REEL.
TAPE CONFORMS TO ANSI/EIA-481
 - LIFE TEST: 5,000 CYCLES.
 - MATERIALS:
HOUSING - LCP, BLACK
SHELL AND OUTER SHIELD - STAINLESS STEEL, NICKEL PLATED
CONTACTS - BRASS, GOLD FLASH IN CONTACT AREA, TIN IN SOLDER AREA
 - ELECTRICAL CHARACTERSTICS
CURRENT RATING: 0.5 AMP
VOLTAGE RATING: 40V
 - MECHANICAL CHARACTERISTICS
INSERTION FORCE: 4.5Kgf MAX
WITHDRAWAL FORCE: 1.0~1.4 Kgf (INITIAL)
 - OPERATING TEMPERATURE: -25°C TO +85°C
 - THIS PRODUCT IS RoHS COMPLIANT.

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH SPEC No.						MATERIAL SPEC No.			
						FIRST USED ON				SCALE 3.5:1		Switchcraft®			
						DATE DRAWN	BY	CHKD		APVD					
						9/4/20	FM	FM 9/4/20		TJK 10/13/20					
A	28330	10/22/20	PC	TJK											
REV	ECO NUMBER	DATE	BY	APVD											
REVISIONS															
					DO NOT SCALE DRAWING										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAVHD19ETR](#)