




- NOTES:
- PARTS ARE SUPPLIED PACKED IN PLASTIC TRAYS.
 - LIFE TEST: 5,000 CYCLES.
 - MATERIALS:
HOUSING - LCP, BLACK
SHELL AND OUTER SHIELD - STAINLESS STEEL, NICKEL PLATED
CONTACTS - BRASS, GOLD FLASH IN CONTACT AREA, TIN IN SOLDER AREA
 - ELECTRICAL CHARACTERISTICS
CURRENT RATING: 0.5 AMP
VOLTAGE RATING: 40V
 - MECHANICAL CHARACTERISTICS
INSERTION FORCE: 4.5Kgf MAX
WITHDRAWAL FORCE: 1.0~1.4 Kgf (INITIAL)
 - OPERATING TEMPERATURE: -25°C TO +85°C
 - THIS PRODUCT IS RoHS COMPLIANT.

A	28330	10/22/20	PC	TJK
REV	ECO NUMBER	DATE	BY	APVD
REVISIONS				

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES [mm]

- TWO PLACE DECIMALS ±0.02 [0.5]

- THREE PLACE DECIMALS ±0.005 [0.13]

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 3.5:1		Switchcraft®			
DATE DRAWN	BY	CHKD	APVD						
9/4/20	FM	FM	TJK						
				9/4/20		10/13/20		SHEET 1 OF 1	
NAME HDMI TYPE A VERTICAL FEMALE CONNECTOR, RoHS					PART No. RAVHD19				REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAVHD19](#)