



- NOTES:
1. MAY BE USED WITH PC BOARD THICKNESSES RANGING FROM 0.054 - 0.070.
  2. THESE DIMENSIONS VARY DEPENDING ON PCB THICKNESS. DIMENSIONS SHOWN ARE FREE STATE AS SHIPPED.
  3. MATERIAL SPECIFICATIONS:  
HOUSING - THERMOPLASTIC, BLACK.  
SPRINGS - SPECIAL COPPER ALLOY, TINNED.
  4. THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	DIM "A"		DIM "B"	
	FREE STATE	WITH 0.062 THICK PCB	FREE STATE	WITH 0.062 THICK PCB
SN49A11	0.504	0.492	0.720	0.708
SN49A12A	0.504	0.492	0.720	0.708
SN49A12B	0.504	0.492	0.720	0.708
SN49A14B	0.504	0.492	0.720	0.708

C	CAD REDRAW ECO #27409	11/17/14	PC	TJK	
REV	ECO NUMBER	DATE	BY	APVD	
REVISIONS					

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES

- TWO PLACE DECIMALS ±0.02

- THREE PLACE DECIMALS ±0.005

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 3:1		<div>Switchcraft®</div>			
DATE DRAWN	BY	CHKD	APVD						
08/17/84	VL	VL	KR						
					SHEET 1 OF 1				
NAME PHONE JACK INSULATED BUSHING					PART No. SN49A SERIES				REV C

CUSTOMER DRAWING

Switchcraft®

SHEET 1 OF 1

PART No. SN49A SERIES

REV C

SolidWorks CAD File

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[SN49A12B](#)