



- NOTES:**
1. MOUNTING HARDWARE SHIPPED UNASSEMBLED.
 2. RATED 15 AMP, 24 VOLT DC AT 105° C (CURRENT CARRY ONLY) WHEN USING 14 AWG STRANDED CONDUCTOR CABLE.
 3. IP68 RATED WHEN MATED TO S15KS SERIES PLUGS.
 4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH				MATERIAL		
						SPEC No.				SPEC No.		
						FIRST USED ON			SCALE 1.5:1		Switchcraft®	
						DATE DRAWN	BY	CHKD	APVD			
A	28515	7/18/22	TJK	TJK	5-10-19	SRC	6-29-22	SRC TJK 7/25/22				
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.	REV	
REVISIONS					DO NOT SCALE DRAWING	15 AMP JACK ASSEMBLY. RoHS					ST15S	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[ST15S](#)