

# Switchcraft®

## 3-Way Dual Isolated Audio Splitters



### Features

- Dual transformer isolated...  
(2 isolated and 1 direct output for each of the 8 inputs)
- Line level pad on each input channel allowing either mic or line level audio.
- Ground lift on each isolated output helps eliminate ground loops.
- Wide variety of I/O options geared towards live sound and permanent installation.

### 3-Way Dual Isolated Audio Splitters

The RMAS8C, RMAS8C*PRO*, RMAS8 and RMAS8*PRO* are 8 input, 24 output (3-way) dual transformer isolated audio splitters. A line level pad on each of the 8 input channels allows connection of either mic or line level audio signals. Ground lift switches on each of the 16 transformer isolated outputs help eliminate ground loops. Additionally, a set of 8 direct (non-isolated) outputs enable a permanent and secure connection to phantom power supplies.

I/O varies by unit and consists of standard 3-Pin XLR, Euro Block, or DB25 (TASCAM Pinout).

The RMAS8C*PRO* and RMAS8*PRO* feature JENSEN magnetically shielded (MU Metal) dual isolated audio transformers.

Made in Chicago, USA 



# Switchcraft®

## 3-Way Dual Isolated Audio Splitters

### RMAS8C / RMAS8CPRO

- Designed for permanent installation.
- Line level pad on each input.
- Ground lift on each isolated output.
- Euro block I/O.
- RMAS8CPRO comes standard with JENSEN (MU Metal) isolation transformers.



### RMAS8

- Designed for mobile / live sound.
- Line level pad on each input.
- Ground lift on each isolated output.
- XLR and DB25 I/O.



### RMAS8PRO

- Designed for mobile / live sound.
- Line level pad on each input.
- Ground lift on each isolated output.
- XLR, DB25, and Euro block I/O.
- JENSEN (MU Metal) isolation transformers.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[RMAS8C](#) [RMAS8CPRO](#)