



AS VIEWED FROM FRONT MATING VIEW



TA TINI QG CORD PLUG
M MALE
SH SHIELDED HANDLE
F SPRING FLEX RELIEF

NUMBER OF CONTACTS
3 - 3 CONTACTS
4 - 4 CONTACTS
5 - 5 CONTACTS
6 - 6 CONTACTS
7 - 7 CONTACTS
8 - 8 CONTACTS

CONTACT PLATING
BLANK - SILVER (STANDARD)
AU - GOLD



TA3MSHF SHOWN

CUSTOMER DRAWING

NOTES:

1. MATERIALS:
HOUSING - COPPER ALLOY, NICKEL PLATED
CONTACTS - COPPER ALLOY, SILVER OR GOLD PLATED
INSERT - THERMOPLASTIC, DARK BROWN
INSULATOR - THERMOPLASTIC, DARK BROWN
CABLE CLAMP/GROUND TERMINAL - STEEL, ELECTRO-TIN PLATED
TUBULAR INSULATOR - FISH PAPER
HANDLE - COPPER ALLOY, NICKEL PLATED
SPRING FLEX RELIEF - STAINLESS STEEL

2. THIS PRODUCT IS RoHS COMPLIANT.

| | | | | | | | | | |
|--|--|--|--|--------------------------------------|--|--|----|----------------|----------|
| | | | | | THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY. | | | | |
| | | | | UNLESS OTHERWISE SPECIFIED | | SIZE | | WIDTH | |
| | | | | 1. ALL DIMENSIONS IN INCHES [mm] | | FINISH | | MATERIAL | |
| | | | | - TWO PLACE DECIMALS ±0.02 [0.5] | | SPEC No. | | SPEC No. | |
| | | | | - THREE PLACE DECIMALS ±0.005 [0.13] | | FIRST USED ON | | SCALE 2:1 | |
| | | | | | | DATE DRAWN | BY | CHKD | APVD |
| | | | | | | 07/15/09 | BS | TJK | TJK |
| | | | | | | | | 02/04/16 | 02/04/16 |
| | | | | | | NAME | | PART No. | |
| | | | | | | MALE TINI QG SHIELDED W/ FLEX RELIEF, RoHS | | TA_MSHF SERIES | |
| | | | | | | | | REV | |
| | | | | | | | | A | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[TA3MSHF](#) [TA4MSHF](#) [TA5MSHF](#) [TA6MSHF](#) [TA7MSHF](#) [TA8MSHF](#)