



TRS AND TRS WIRING CHART							
JACKET COLOR	H.S. TUBING MARKING	END "A" TRS PLUG			END "B" TRS PLUG		
		RED	BLACK	BARE	RED	BLACK	BARE
BROWN	CHANNEL 1	TIP	RING	SLEEVE	TIP	RING	SLEEVE
RED	CHANNEL 2	TIP	RING	SLEEVE	TIP	RING	SLEEVE
ORANGE	CHANNEL 3	TIP	RING	SLEEVE	TIP	RING	SLEEVE
YELLOW	CHANNEL 4	TIP	RING	SLEEVE	TIP	RING	SLEEVE
GREEN	CHANNEL 5	TIP	RING	SLEEVE	TIP	RING	SLEEVE
BLUE	CHANNEL 6	TIP	RING	SLEEVE	TIP	RING	SLEEVE
PURPLE	CHANNEL 7	TIP	RING	SLEEVE	TIP	RING	SLEEVE
GRAY	CHANNEL 8	TIP	RING	SLEEVE	TIP	RING	SLEEVE

PART NUMBER	CABLE LENGTH "X"
TRS05TRS	5.00 FT +/- 1.50 IN
TRS10TRS	10.00 FT +/- 1.50 IN

NOTES:

- B

1. BREAKOUT CABLE LENGTH IS 18.00 +/- 0.75 IN.
- B

2. CABLE IS SHIPPED COILED AND PACKAGED IN A BAG.
- B

3. MATERIALS:
CABLE - COPPER, THERMOPLASTIC
TRS PLUG:
INSULATING WASHERS - THERMOPLASTIC
PLUG BODY AND TIP ROD - COPPER ALLOY, NICKEL PLATED
INSULATORS - MYLAR
TERMINALS - COPPER ALLOY, ELECTRO-TINNED
HANDLE - COPPER ALLOY, NICKEL PLATED
- B

4. THIS PRODUCT IS RoHS COMPLIANT.

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.															
						SIZE	WIDTH		MULT		LBS/M		TEMPER								
						FINISH						MATERIAL									
						SPEC No.						SPEC No.									
						FIRST USED ON				SCALE		<div>Switchcraft®</div>									
										1:2											
B	26637	10/11/10	RS	TJK		DATE DRAWN	BY	CHKD		APVD		SHEET 1 OF 1									
A	25983	10/30/08	RS	TJK	4/14/08	JGK	RS		TJK												
REV	ECO NUMBER	DATE	BY	APVD	NAME						PART No.		REV								
REVISIONS					DO NOT SCALE DRAWING					TRS PLUG TO TRS PLUG, RoHS						TRS_ _TRS				B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[TRS05TRS](#) [TRS10TRS](#)