



DIMENSIONS SHOWN FOR REFERENCE ONLY



- NOTES:
1. MEETS SMPTE 2082-1
CHARACTERISTIC IMPEDANCE: 75 OHMS
CONTACT RESISTANCE: 50 MILLIOHMS MAX.
 2. MATERIAL:
BODY: COPPER ALLOY, NICKEL PLATED.
CONTACT PIN: COPPER ALLOY, GOLD PLATED.
SPRING: BERYLLIUM COPPER, NICKEL PLATED.
TINE CONTACT: BERYLLIUM COPPER, GOLD PLATED.
INSULATOR: TEFLON
FERRULE: COPPER ALLOY, NICKEL PLATED.
 3. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
						SIZE	WIDTH		MULT	LBS/M	TEMPER		
						FINISH				MATERIAL		SEE NOTES	
						SPEC No.				SPEC No.			
						FIRST USED ON			SCALE		Switchcraft®		
									4:1				
						DATE DRAWN	BY	CHKD	APVD				
A	28195	08/29/19	PC	TJK		04/05/17	PNK	04/05/17	04/05/17				
							PNK	SRC					
REV	ECO NUMBER	DATE	BY	APVD	NAME				PART No.		REV		
REVISIONS					DO NOT SCALE DRAWING		UHD DIN 1.0/2.3 PLUG 75 OHMS, 4855R, RoHS				UHDDIN55		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[UHDDIN55](#)