



STRIPPING DIMENSIONS FOR 4505R CABLE



NOTES:

1. MUST BE ROHS COMPLIANT.
2. MUST BE USEABLE TO 12GHZ.
3. ALL DIMENSIONS ARE REF.
4. CRIMP CONTACT PIN WITH 0.042 SQUARE.
5. CRIMP FERRULE WITH 0.255 HEX.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH	MULT	LBS/M	TEMPER		
						FINISH			MATERIAL			
						SPEC No.			SPEC No.			
						FIRST USED ON		SCALE		Switchcraft®		
						*		1:1				
A	28255	2/21/20	TJK	TJK	DATE DRAWN	BY	CHKD	APVD				
					10/7/19	SRC	TJK	TJK				
							5/4/20	5/4/20				
REV	ECO NUMBER	DATE	BY	APVD	NAME				PART No.	REV		
					PLUG, MICRO BNC FOR 4505R CABLE				UHDMB05	A		
REVISIONS					DO NOT SCALE DRAWING							

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[UHDMB05](#)