




NOTES:



- DRAWING SHOWS ONLY TS CONFIGURATION.
- IP RATING: IP66, SEALED WHEN MATED.
- HANDLE MATERIAL: NYLON AND RUBBER.
- USE THE FOLLOWING TABLE TO DETERMINE THE SUITABLE HANDLE FOR A SPECIFIC CABLE:

Cable OD / Inches	140	170	171	200	201	230	231	260	261	290
PLUG SUFFIX	..S15	..S18	..S22	..S25	..S28					

- USE THE FOLLOWING TABLE TO DETERMINE THE SUITABLE HEX NUT AND WASHER, FOR A SPECIFIC PANEL THICKNESS:

Panel thickness / Inches	0.050	0.055	0.060	0.065	0.070	0.075	0.080	0.085	0.090	0.095	0.100	0.105	0.110	0.115	0.120	0.125
Kit part number	W07 (LARGE)										W11 (SMALL)					
Washer (K180)	yes	yes	yes	yes	yes	no	no	no	no	yes	yes	yes	yes	yes	no	no

- RECOMMENDED MOUNTING HOLE DIMENSION:



- MAKE SURE THAT THE PLUG IS TIGHTENED ALL THE WAY INTO THE HANDLE TO GUARANTEE PROPER SEAL, MOUNTING THE PLUG MAY REQUIRE EXTRA FORCE TO OVERCOME THE RUBBER EDGE INTERFERENCE.
- RECOMMENDED WORKING TEMPERATURE:
-20 TO 50 C°
- THIS PRODUCT IS RoHS COMPLIANT.

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE *	WIDTH *	MULT *	LBS/M *	TEMPER *
					FINISH *	MATERIAL *			
					SPEC No. *	SPEC No. *			
					FIRST USED ON *	SCALE 1:4			
					DATE DRAWN	BY	CHKD	APVD	
					11/25/19	NS	NS	SRC	
							11/25/19	11/25/19	
					NAME			PART No.	REV
					SEALED 0.25" PLUG AND JACK			11W07-W11 250S15-S28	0A

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

W07 W11