



MFG. ENG.	APPROVED BY:	DATE:	QA	APPROVED BY:	DATE:
-----------	--------------	-------	----	--------------	-------

- NOTES:
- ALL PARTS TO BE BULK PACKED UNLESS NOTED.
 - INSTA CLICK CABLE END ASSEMBLY IS SUPPLIED AS A KIT. SEE KIT DRAWING. CONTACTS SUPPLIED UNASSEMBLED FOR CRIMP AND ASSEMBLED FOR SOCKET VERSIONS
 - ALL DIMENSIONS ARE REFERENCED IN INCHES [MM], WITHIN ± 0.015 UNLESS NOTED.
 - SIZE #12, 2 POSITION CRIMP CONTACTS ASSEMBLY IS BEEN SHOWN AS EXAMPLE. VISIT PART NUMBERING SYSTEM CHART TO VISIT VARIOUS SELECTIONS




W3182-2SG-P-3XX SHOWN
MATING VIEW



CABLE END CONN KIT
MATL:
HOUSING- THERMOPLASTIC, BLACK
COUPLING RING- THERMOPLASTIC, BLACK
O-RING - RED SILICONE
INTERNAL SPRING - STAINLESS STEEL



#12 SOLDER CONTACTS SHOWN HERE
MATL: COPPER ALLOY, GOLD PLATED



SLEEVE
MATL: THERMOPLASTIC, BLACK

BACKSHELL
MATL: THERMOPLASTIC, BLACK

GROMMET
MATL: SANTOPRENE, BLACK
W3180-2SG-P-315 0.156 ID FOR CABLES 0.15 - 0.17 [3.5 - 4.3mm]OD
W3180-2SG-P-318 0.187 ID FOR CABLES 0.18 - 0.20 [4.6 - 5.1mm]OD
W3180-2SG-P-321 0.225 ID FOR CABLES 0.21 - 0.23 [5.3 - 5.8mm]OD
W3180-2SG-P-324 0.250 ID FOR CABLES 0.24 - 0.27 [6.1 - 6.8mm]OD
W3180-2SG-P-328 0.285 ID FOR CABLES 0.28 - 0.29 [7.1 - 7.4mm]OD
W3180-2SG-P-330 0.312 ID FOR CABLES 0.30 - 0.32 [7.6 - 8.1mm]OD


PART NUMBER SYSTEM
W 3 X 8 X - X SG -P- 3 XX

CONTACT SIZES
1' - SIZE #12
2' - SIZE #20
3' - SIZE #16


CONTACTS STYLE
0' - CRIMP
2' - SOLDER

CONTACT POSITIONS
POSITION 2, 3 & 4 (AVAILABLE IN SIZE #12)
POSITION 4, 5 & 6 (AVAILABLE IN SIZE #16)
POSITION 4,5,6,7,8,9,10,11&12 (AVAILABLE IN SIZE #20)


15 - CABLE OD 0.15 - 0.17 [3.8 - 4.3mm]
18 - CABLE OD 0.18 - 0.20 [4.6 - 5.1mm]
21 - CABLE OD 0.21 - 0.23 [5.3 - 5.8mm]
24 - CABLE OD 0.24 - 0.27 [6.1 - 6.8mm]
28 - CABLE OD 0.28 - 0.29 [7.1 - 7.4mm]
30 - CABLE OD 0.30 - 0.32 [7.6 - 8.1mm]




W3182-2SG-P-3XX SHOWN
WIRE VIEW




W3182-4SG-P-3XX
MATING VIEW




W3182-3SG-P-3XX
MATING VIEW




W3182-2SG-P-3XX
MATING VIEW




W3382-6SG-P-3XX
MATING VIEW




W3382-5SG-P-3XX
MATING VIEW




W3382-4SG-P-3XX
MATING VIEW




W3282-9SG-P-3XX
MATING VIEW




W3282-8SG-P-3XX
MATING VIEW




W3282-7SG-P-3XX
MATING VIEW



W3282-6SG-P-3XX
MATING VIEW



W3282-5SG-P-3XX
MATING VIEW



W3282-4SG-P-3XX
MATING VIEW

0A		AM		04/05/22		CUSTOMER DRAWING											
REV.		INIT.		DATE		DESCRIPTION											
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED. ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 ▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						ORIG. DRAWN BY:			DATE:			CONXALL 601 E. WILDWOOD VILLA PARK, IL 60181					
						AM			04/05/22								
						CHECKED BY:			TITLE: CABLE END CONNECTOR ASSEMBLY (2-4) #12, (4-6) #16, (4-12) #20 SKT CONTACTS MULTI CONX INSTA CLICK STANDARD PRODUCT								
						APPROVED BY:											
						SCALE		SIZE		SHEET							
						NTS		B		1 OF 1							
						FILE:		DIRECTORY:		PART NUMBER:		W3X8X-XSG-P-3XX					
						FILE NAME		SLW									
												REV 0A					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[W3280-10SG-P-328](#) [W3282-4SG-P-331](#) [W3180-3SG-P-3DC](#) [W3280-11SG-P-321](#) [W3182-2SG-P-3DC](#) [W3182-3SG-P-5DC](#) [W3280-10SG-P-3DC](#) [W3280-12SG-P-318](#) [W3282-12SG-P-318](#) [W3280-12SG-P-324](#) [W3282-12SG-P-324](#) [W3280-11SG-P-330](#) [W3280-12SG-P-335](#) [W3282-10SG-P-3DC](#) [W3180-2SG-P-5DC](#) [W3182-3SG-P-335](#) [W3182-4SG-P-3DC](#) [W3280-12SG-P-328](#) [W3280-7SG-P-3DC](#) [W3282-10SG-P-328](#) [W3182-3SG-P-323](#) [W3280-11SG-P-324](#) [W3182-3SG-P-3DC](#) [W3280-11SG-P-3DC](#) [W3282-11SG-P-321](#) [W3282-11SG-P-324](#) [W3282-10SG-P-321](#) [W3282-12SG-P-328](#) [W3282-8SG-P-3DC](#) [W3280-10SG-P-318](#) [W3280-12SG-P-321](#) [W3280-6SG-P-320](#) [W3282-10SG-P-318](#) [W3182-3SG-P-331](#) [W3280-12SG-P-3DC](#) [W3280-9SG-P-3DC](#) [W3282-10SG-P-330](#) [W3282-11SG-P-3DC](#) [W3280-11SG-P-318](#) [W3182-2SG-P-5DC](#) [W3280-10SG-P-330](#) [W3280-8SG-P-3DC](#) [W3282-9SG-P-3DC](#) [W3280-5SG-P-3DC](#) [W3282-11SG-P-328](#) [W3282-11SG-P-330](#) [W3180-2SG-P-3DC](#) [W3282-12SG-P-321](#) [W3180-4SG-P-3DC](#) [W3280-12SG-P-330](#) [W3280-6SG-P-3DC](#) [W3280-10SG-P-321](#) [W3280-10SG-P-324](#) [W3282-10SG-P-324](#) [W3282-12SG-P-330](#) [W3282-12SG-P-3DC](#) [W3282-7SG-P-3DC](#) [W3280-4SG-P-3DC](#) [W3282-11SG-P-318](#) [W3282-4SG-P-3DC](#) [W3282-6SG-P-3DC](#) [W3280-11SG-P-328](#) [W3282-5SG-P-3DC](#)